

# Two-Door Floorstand Type 4X 1/4-Turn Latches, 60x60x18, Brushed, SS304

## CATALOG NUMBER

**A60H6018SSLPQT**



This two-door stainless steel enclosure with quarter-turn latches is designed to house electronic controls and components. It provides protection from noncorrosive or mildly corrosive elements in both indoor and outdoor environments. Typical applications are in the food and beverage, packaging, water, petroleum and chemical processing industries.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC: Type 3R, 4, 4X, 12

Number E61997

IEC 60529, IP66

Meets NEMA Type 3RX requirements

## CERTIFICATIONS



## FEATURES

Floor-standing enclosure with 1/4 turn latching

Seams continuously welded and ground smooth

Flange trough collar on all four sides of door openings

Seamless foam-in-place one-piece gasket provides water-, oil- and dust-tight seal against contaminants

Black die-cast quarter-turn latches with slotted insert provided on three sides of each door

Concealed hinges provide 180-degree door opening and allow easy door removal and cleaning of hinge area

Bolt-on 12-in.-high stainless steel floor stands

Heavy-duty Type 316L stainless steel lifting eyes

Collar studs on inside of enclosure back for mounting optional panels

Removable centerpost for easy panel installation

Bonding provisions on doors; grounding studs on body

Data pocket is high-impact plastic attached with pressure-sensitive adhesive

No interior stiffeners to obstruct component mounting

Accessory mounting channel provided in enclosure top

## PRODUCT ATTRIBUTES

---

Article Number: 13718

Height: 60.06in

Width: 60.06in

Depth: 18.06in

Material: Stainless Steel 304

Finish: Brushed #4

Body Thickness: 12ga

Door Thickness: 14ga

Latch Quantity: 10

Weight: 473lb

## ADDITIONAL PRODUCT DETAILS

---

Purchase panels separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**