


Rack Mounting Angle U Style Type RA, Full Length, fits 60x24, Steel

CATALOG NUMBER

A60RA19TH



Rack mounting angles U style Type RA are designed for Free-Stand Enclosures with mounting channel. A pair of full-length rack mounting angles are available for mounting 19-in. (483-mm) and 24-in. (610-mm) rack-mounted equipment.

FEATURES

Type RA rack mounting angles have mounting holes .281 in. (7 mm) in diameter and spaced per EIA 310-D standard

Angles and mounting hardware are plated

All mounting hardware is furnished

Use clip nut package AN1032 to provide tapped holes at desired locations

PRODUCT ATTRIBUTES

Article Number: 74550

Material: Mild Steel

Finish: Zinc Plated

Thickness: 14ga

Fits Enclosure Size: 60.00 x 24.00in

Unit Quantity: 28

For Rack Size: 19in

Weight: 13lb

ADDITIONAL PRODUCT DETAILS

One unit equals 1.75-in (44-mm).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE