nVent | HOFFMAN

We connect and protect

Wiring Trough NEMA Type 1, 6.00x6.00x36.00, Gray, Steel

CATALOG NUMBER

A6636T1T



Screw-Cover Wiring Trough, Type 1 is used for protecting wire and cable distribution, junctions and terminations in a variety of indoor applications where protection against dirt or moist is not needed.

INDUSTRY STANDARDS

UL 870 Listed; File No. E27524

cUL CSA C22.2 No. 26 Listed; File No. E27524

NEMA/EEMAC: Type 1

IEC 60529, IP30

FEATURES

- Keyhole screw slots in cover
- Shipped completely assembled-no end caps to install
- Mounting holes on the back of the enclosure
- Flat cover fastened with plated steel screws
- No gasketing or knockouts

PRODUCT ATTRIBUTES

- Article Number: 11283
- Type: Trough
- Height: 6in
- Width: 6in
- Depth: 36in
- Material: Mild Steel
- Finish: Galvanized
- Thickness: 16ga
- Mounting: 24in
- Mounting: 4in
- Weight: 18.02lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.