

Hinge-Cover Small Drip-Shield Enclosure Type 3R, 6.00x4.00x4.00, Gray, Steel

CATALOG NUMBER

A6R44HCR



Small Drip-Shield Hinged-Cover, Type 3R protects wiring and other electrical components in outdoor applications that require protection from rain, sleet, snow or dripping water. It offers the flexibility of securing enclosure with an optional padlock in its draw-pull catch and weldnuts for optional panel mounting. These enclosures have a size range of 6 x 4 x 4-in. to 12 x 12 x 10-in.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27567

cUL Listed per CSA C22.2 No 94; Type 3R File No. E27567

NEMA/EEMAC Type 3R

IEC 60529, IP32

FEATURES

Drip shield top and seam-free sides, front, and back protect from rain, snow, or sleet

Plated steel hinge has stainless steel pin

Weldnuts provided for mounting optional panels

Provisions for padlocking on zinc-plated draw-pull catch

Knockouts on bottom of enclosure

No gasketing

PRODUCT ATTRIBUTES

Article Number: 13402

Height: 6in

Width: 4in

Depth: 4in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Overall Dimensions: 8.00 x 4.81in

Mounting: 7in

Knockout Pattern: B-C-D

Weight: 3.6lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE