

# Swing-Out Rack Mounting Frame for Free-Stand, fits 72.06x36.06, White, Steel

## CATALOG NUMBER

**A7236SOF19**



Swing-Out Rack Mounting Frames is used for mounting 19-inch (483-mm) rack mounting equipment. The frame pivots within the enclosure to allow access to the back of the mounted equipment. The frame is full-length and can be installed in 72.00-in. (1829-mm) and 90.00-in. (2286-mm) high enclosures that are 30.00-in. (762-mm) or 36.00-in. (914-mm) wide. They can be installed in 60.00-in. (1524-mm) or 72.00-in. (1829-mm) wide enclosures if a center panel support is used. The design features smooth operation and secure positioning anywhere along the horizontal mounting channels. Frame swings from the left side.

## FEATURES

The Swing-Out Rack Mounting Frames have mounting holes tapped #10-32 thread and spaced per EIA 310-D standard  
Plated mounting hardware is provided

## PRODUCT ATTRIBUTES

Article Number: 74410

Height: 72.06in

Width: 36.06in

Material: Mild Steel

Finish: Powder Coated

Color: White

Thickness: 10ga

Unit Quantity: 33

For Rack Size: 19in

Max D: 24.25in

Weight: 74lb

## ADDITIONAL PRODUCT DETAILS

---

One unit equals 1.75-in (44-mm).

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**