

# Two-Door Freestanding Screw-Cover Type 4X, 72x49x24.5, Gray, Fiberglass

## CATALOG NUMBER

**A724925FG**



An economical way to house electronics in corrosive environments, two-door enclosures provide easy access to equipment, larger capacity for control systems and steel reinforcements that ensure stability and strength. These enclosures feature captivated door screws and an optional PowerGlide Handle for secure latching.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12; File No. E61997

Enclosure flammability evaluated per UL 508A

NEMA Type 3, 3R, 4, 4X, 12, 13

IEC 60529, IP66

Meets NEMA Type 3RX requirements

## CERTIFICATIONS



## FEATURES

Fiberglass-reinforced polyester material has excellent temperature and chemical resistance and exhibits outstanding physical properties

Seams are sealed; no holes or knockouts

Fiberglass material is easily punched, drilled, filed or sawed

Models have either a 3-point latching system with handle or stainless steel captivated door screws

Type 316 stainless steel PowerGlide Handle on handle versions

Stainless steel captivated door screws on screw versions

Seamless foam-in-place gasket assures a water-tight and dust-tight seal

Painted steel top, bottom and side internal reinforcements standard; stainless steel corner reinforcements optional

Solid centerpost (not removable) has heavy-gauge stiffener

Heavy-duty Type 316 stainless steel lifting eyes

Hinges are corrosion-resistant fiberglass with Type 316 stainless steel hinge pins

Large data pocket (12.00 x 12.00 in. or 305 x 305 mm) is high-impact thermoplastic

Molded-in angular sealing flange directs water away from gasket area

Material is halogen free

Two white painted, 12-gauge, mild-steel panels included.

## PRODUCT ATTRIBUTES

---

Article Number: 26740

Height: 72in

Width: 49in

Depth: 24.5in

Material: Fiberglass

Finish: Smooth Gloss

Color: Gray

Thickness: 0.22in

Panel Quantity: 2

Weight: 413lb

## ADDITIONAL PRODUCT DETAILS

---

For CALIFORNIA residents only - WARNING: This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm. Please note that by posting this Proposition 65 warning, we are notifying you that one or more of the Proposition 65 listed chemicals may be present in this product. With HOFFMAN's products, the exposure to these chemicals may be of no significant risk to you, but out of caution and to ensure your well-being, we have elected to place this warning on our site to make sure our customers are informed. You can find more information at <http://www.oehha.ca.gov/proposition-65/about-proposition-65>.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**