

Two-Door Floorstand 3-Pt Latch Type 12, 72x72x24, Brushed, SS304

CATALOG NUMBER

A727224USSLP



Designed to house systems incorporating large components or complex mounting configurations. Three-point latching and sealing provide industry-leading protection from dust, dirt, oil and water.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 12; File No. E61997

NEMA/EEMAC Type 12

IEC 60529, IP55

FEATURES

Seams continuously welded and ground smooth; no holes or knockouts

Strong, rigid construction with body stiffeners

Gasketed overlapping doors eliminate need for centerpost

Plated steel 3-point latching mechanism and key-locking handle

Heavy-gauge continuous hinges support each door

Data pocket, provided on door with 3-point latches, is high-impact thermoplastic

12-in. (305-mm) floor stands are bolted to enclosure

Heavy-duty lifting eyes are Type 316 stainless steel

Panel supports

Collar studs for mounting optional panel

Bonding provision on doors; grounding studs on body

Accessory mounting channel in top of enclosure

PRODUCT ATTRIBUTES

Article Number: 84280

Height: 72.06in

Width: 72.06in

Depth: 24.06in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 12ga

Panel Gauge: 11ga

Stiffener Body: 1

Weight: 720lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

Includes frame, door(s), two sides and four lifting eyes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE