

Free-Stand Type 4, 72.06x37.06x24.06, Gray, Steel

CATALOG NUMBER

A72H3724FS



These enclosures are ideal for mounting equipment on panels or racks in indoor or outdoor applications where it is necessary to protect controls and instrumentation from wet, non-corrosive environments.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997

NEMA Type 3, 4, 12, 13

CSA, File No. 42186, Type 4, 12

E.I.A. RS310D

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth; no holes or knockouts

Internal mounting channels welded horizontally at top, bottom and center

Panels and rack-mounting angles can be mounted anywhere along channels

Return flange around three sides of door and along enclosure opening excludes liquids and contaminants

Stainless steel door clamps assure water-tight seal

Hasp and staple provided for padlocking

Data pocket is high-impact thermoplastic

Lifting eyes for easy handling

Oil-resistant door gasket

Bonding provision on door

Provision for mounting fluorescent light

PRODUCT ATTRIBUTES

Article Number: 27470

Height: 72.06in

Width: 37.06in

Depth: 24.06in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 12ga

Rack Unit Quantity: 35

Weight: 406lb

ADDITIONAL PRODUCT DETAILS

Order panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE