

# Freestand Disconnect 1-Door 1/4-Turn 3pt Latch Type 4X, 72x39x24, Brushed, SS304

## CATALOG NUMBER

**A72HXS3924SSLPQT**



This single door, stainless steel, disconnect enabled enclosure with quarter-turn latches is designed to house electronic controls and components. It provides protection from non-corrosive or mildly corrosive elements in both indoor and outdoor environments. Typical applications are in the pharmaceutical, food and beverage, packaging, water, petroleum and chemical processing industries.

## INDUSTRY STANDARDS

UL508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC: Type 3R, 4, 4X, 12

IEC 60529, IP66

Meets NEMA Type 3RX

## CERTIFICATIONS



## FEATURES

Disconnect enabled enclosure is designed to house electronic controls

Seams continuously welded and ground smooth

Flange trough collar on all four sides of door openings

Seamless foam-in-place one-piece gasket provides water-, oil- and dust-tight seal against contaminants

Heavy-duty three-point latching mechanism on each door, operated by nVent HOFFMAN's black die-cast PowerGlide padlocking handle; back die-cast quarter-turn latches with slotted insert provided on the top and bottom of each door

Black Die-Cast PowerGlide handle has integral screwdriver defeater

Collar studs on inside of enclosure back for optional mounting panels

Concealed stainless steel hinges provide 180-degree door opening and allow easy door removal and cleaning of hinge area

Heavy-duty Type 316L stainless steel lifting eyes

Bonding provision on door; grounding stud on body

High-impact plastic Data Pocket kit included with enclosure

Accessory mounting channel provided in enclosure

## PRODUCT ATTRIBUTES

---

Article Number: 19172

Height: 72.06in

Width: 38.5in

Depth: 24.06in

Material: Stainless Steel 304

Finish: Brushed #4

Thickness: 14ga

Weight: 310lb

## ADDITIONAL PRODUCT DETAILS

---

Purchase panels separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**