

Rack Mounting Angle L Style Type RP, Half Length, fits 72x24, Steel

CATALOG NUMBER

A72RP24F6



Rack mounting angles L style Type RP are designed for Free-Stand Enclosures with mounting channel. A pair of full-length or half-length rack mounting angles are available for mounting 19-in. (483-mm) and 24-in. (610-mm) rack-mounted equipment.

FEATURES

Type RP rack mounting angles have mounting holes tapped #10-32 thread and spaced per EIA 310-D standard

Angles and mounting hardware are plated

All mounting hardware is furnished

PRODUCT ATTRIBUTES

Article Number: 21430

Material: Mild Steel

Finish: Zinc Plated

Thickness: 10ga

Fits Enclosure Size: 72.00 x 24.00in

For Rack Size: 19in

Unit Quantity: 18

Weight: 9.8lb

ADDITIONAL PRODUCT DETAILS

One unit equals 1.75-in (44-mm).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE