

# Rack Mounting Angle L Style Type RP, Full Length, fits 72x30, Steel

## CATALOG NUMBER

**A72RP30F5**



Rack mounting angles L style Type RP are designed for Free-Stand Enclosures with mounting channel. A pair of full-length or half-length rack mounting angles are available for mounting 19-in. (483-mm) and 24-in. (610-mm) rack-mounted equipment.

## FEATURES

Type RP rack mounting angles have mounting holes tapped #10-32 thread and spaced per EIA 310-D standard

Angles and mounting hardware are plated

All mounting hardware is furnished

## PRODUCT ATTRIBUTES

Article Number: 21440

Material: Mild Steel

Finish: Zinc Plated

Thickness: 10ga

Fits Enclosure Size: 72.00 x 30.00in

For Rack Size: 24in

Unit Quantity: 35

Weight: 22lb

## ADDITIONAL PRODUCT DETAILS

One unit equals 1.75-in (44-mm).

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**