

# Two-Door Floorstand NEMA Clamps Type 4X, 74x60x12, Brushed, SS316

## CATALOG NUMBER

**A74H6012SS6LP**



This two-door enclosure provides industry-leading protection for systems incorporating large components or complex mounting configurations in highly corrosive environments. It is typically used in food processing plants, pharmaceutical manufacturing facilities, petrochemical plants, pulp and paper processing and water treatment facilities.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA Type 3, 3R, 4, 4X, 12, 13

CSA File No. 42186: Type 4, 4X, 12

IEC 60529, IP66

Meets NEMA Type 3RX requirements

## CERTIFICATIONS



## FEATURES

Freestanding enclosure with NEMA style clamps

Seams continuously welded and ground smooth; no holes or knockouts

Backs are 10 or 12 gauge stainless steel with x-form stiffeners

Removable centerpost for easy panel installation

Panel supports

Stainless steel screws and clamps on three sides of each door assure water-tight seal

Rolled lip around entire door opening excludes liquids and contaminants

Heavy-gauge stainless steel continuous hinge

Data pocket is high-impact thermoplastic

12-in. (305-mm) floor stands are bolted onto enclosure

Hasp and staple for padlocking

Seamless foam-in-place gasket provides oil-tight and dust-tight seal against contaminants

Collar studs provided for mounting optional panels

External hardware manufactured of Type 316 stainless steel

Bonding provision on doors; grounding studs on body

Accessory mounting channel provided in enclosure top

Type 316L stainless steel lifting eyes

## PRODUCT ATTRIBUTES

---

Article Number: 79760

Height: 74.06in

Width: 60.06in

Depth: 12.06in

Material: Stainless Steel 316L

Finish: Brushed #4

Thickness: 12ga

Clamp Quantity: 18

Weight: 504lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**