

CT Cabinet Hinged-Cover Bar-Mount Lugs Type 3Rs, 48.07x30.00x11.00, Gray, Steel

CATALOG NUMBER

A800HCTB



These cabinets are available in a variety of sizes, models and instrument current transformer mounting methods to fit a wide range of applications.

INDUSTRY STANDARDS

UL 50, 50E Listed; File No. E27525, E27567

cUL Listed per CSA C22.2 No 94; File No. E27525, E27567

NEMA Type 3R

IEC 60529, IP32

Models with termination lugs also have UL414, File No. E240312

FEATURES

Quarter-turn latch

Lift-off hinges

Doorstop

Line and load lugs

Staple for seal or padlock

Enclosures are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 14575

Height: 48.07in

Width: 30in

Depth: 11in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 12ga

Door Thickness: 14ga

Number of Phases: 3Ph

Wire Size: (3) 1/0 - 750 MCM; (6) 1/0 - 250 MCM

Weight: 181lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE