

# CT Cabinet with Lugs Type 3R, 3-Phase 800-1200 Amp, Gray, Steel

## CATALOG NUMBER

**A800NECT**



CT Cabinet, 3-Phase 400-1200 Amp with Lugs, Type 3R, are used in indoor or outdoor applications. These cabinets provide an assembly solution for three-phase service from 400-1200 amp line load terminations for each phase and neutral. Hardware to mount a bar-style current transformer is included.

## INDUSTRY STANDARDS

UL 414 Listed; Type 3R; File No. E240312

UL 50, 50E Listed; Type 3R; File No. E27525

cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R

IEC 60529, IP 32

## FEATURES

Double door with 3-point latch includes padlock feature

Lift-off hinges for removable doors

Mechanical lugs provided for three-phase line-load connections plus neutral

Ground lug

Catalog number A1200NECT includes panel-mounting provisions for voltage transformer (VT)

Embossed mounting holes

No gasketing or knockouts

Enclosures are finished with paint over plated surfaces

## PRODUCT ATTRIBUTES

Article Number: 14923

Height: 36in

Width: 36in

Depth: 12in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 14ga

Door Thickness: 14ga

Mechanical Lug Capacity: Each Phase (3) 750MCM-1/0

Weight: 149lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**