

Continuous Hinge Enclosure Clamps CH Type 12, 8x6x3.50, Gray, Mild Steel, Short

CATALOG NUMBER

A8063CHS



This easy-to-open, continuous hinge enclosure features screw-down clamps for secure closure and can be used in a wide variety of applications.

INDUSTRY STANDARDS

*UL 50, 50E Listed; Type 12, 13; File No. E27567

cUL Listed per CSA 22.2 No. 94; Type 12, 13; File No. E27567

*UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA 22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12 and 13

CSA, File No. 42184: Type 12

IEC 60529, IP65

FEATURES

Seams continuously welded and ground smooth

Continuous hinge

Screw-down door clamps

Bonding provision on door

External wall-mounting brackets for easy installation

Oil-resistant gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

PRODUCT ATTRIBUTES

Article Number: 29271

Height (H): 8in

Width (W): 6in

Depth (D): 3.5in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness (T): 14ga

Mounting (G x H): 8.75 x 4.00in

Overall Dimensions (L x W): 9.50 x 6.94in

Weight: 5lb


ADDITIONAL PRODUCT DETAILS

Catalog numbers ending in "S" are hinged on short side.

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

*Items A404CH, A604CH, A4044CH, and A6044CH are UL 508A Listed. All other items are UL 50, 50E Listed.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE