

Continuous Hinge with Clamps Junction Box EMC Type 4X, 8x6x4, Brushed, SS304

CATALOG NUMBER

A8064CHEMCSS



Use this enclosure in corrosive indoor or outdoor applications to contain stray electromagnetic interference (EMI) signals produced by internal components and to shield those components from external EMI/RFI interference.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 4, 4X, 12; File No. E27567

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File No. E27567

UL 508A Listed; Type 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 4, 4X, 12, 13

CSA File No. 42184; Type 4, 4X, 12

IEC 60529, IP66

FEATURES

Seams continuously welded and ground smooth

Seamless foam-in-place gasket adjacent to monel mesh assures water-tight, dust-tight and EMI seal

Stainless steel screws and clamps

Removable door with continuous hinge

Weldnuts provided for mounting optional panels and terminal kits

Bonding provision on door

PRODUCT ATTRIBUTES

Article Number: 25809

Height: 8in

Width: 6in

Depth: 4in

Material: Stainless Steel 304

Finish: Brushed #4

Body Thickness: 14ga

Door Thickness: 16ga

Overall Dimensions: 9.50 x 6.94in

Mounting: 8.75 x 4.00in

Weight: 5.46lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE