

Lift-Off Clamp Cover Enclosure Type 12, 8.00x8.00x4.00, Gray, Mild Steel

CATALOG NUMBER

A808LP



With a chain-secured, lift-off clamp cover, this enclosure meets basic functionality requirements for housing controls and instrumentation.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 12, 13; File No. E27525

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E27525

UL 508A Listed; Type 12, 13; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 12, 13; File No. E61997

NEMA/EEMAC Type 12 and 13

CSA, File No. 42184: Type 12

IEC 60529, IP65

FEATURES

Seams continuously welded and ground smooth

Screw-down clamps

Lift-off cover

Bonding provision on cover

Chain holds cover to box when cover is removed

Oil-resistant gasket

Weldnuts provided for mounting optional panels and terminal block kits in size 6.00 x 4.00 in. (152 x 102 mm) and larger

External wall-mounting brackets

PRODUCT ATTRIBUTES

Article Number: 29255

Height: 8in

Width: 8in

Depth: 4in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Mounting: 8.75 x 6.00in

Overall Dimensions: 9.50 x 8.94in

Weight: 14.8lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately. Optional stainless steel, conductive, composite and aluminum panels are available for most sizes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE