

Free-Stand Disconnect with QR Hinge Type 4, 84.12x40.25x18.12, Gray, Steel

CATALOG NUMBER

A84XM4018FTCLP4



Simple, heavy-duty and cost-effective with easy door removal and re-installation, this disconnect enclosure can be ordered with one to three doors to fit a range of indoor and outdoor applications

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12, 3R; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12, 3R; File No. E61997

NEMA/EEMAC Type 4, 12, 3R

IEC 60529, IP66

FEATURES

Quick-release continuous hinge

Seams continuously welded and ground smooth

Body stiffeners in larger enclosures for extra rigidity

Body flange trough excludes liquids and contaminants

Heavy-duty lifting eyes anchor into reinforced top

Removable centerposts permit easy panel installation

Heavy-duty 3-point latching mechanism operated by padlocking handle on all doors

Ends of latch rods have rollers for easier door closing

Panel supports

Data pocket is high-impact thermoplastic

Oil-resistant gasket

Master door is far right-hand door on all enclosures

Defeater on primary door requires a screwdriver to open

Mechanical interlock activated by primary door prevents secondary doors from being opened first; doors can be closed in any order

Universal cutout on right flange provides mounting for most disconnect operators by using operator adapters

Models do not include panels. Painted or conductive panels sold separately.

Includes door hardware

PRODUCT ATTRIBUTES

Article Number: 27807

Height: 84.12in

Width: 40.25in

Depth: 18.12in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 11ga

Weight: 498lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

Catalog weights and dimensions are careful estimates but not guaranteed.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE