

Drip-Shield Hinged Lift-Off Cover Type 3R, 8.00x6.00x4.00, Gray, Steel

CATALOG NUMBER

A8R64HCLO



Drip-Shield Hinged Lift-Off Cover, Type 3R features a removable cover for easy mounting and access with padlock pull catch latches. It protects components in outdoor and other applications subject to rain, sleet, snow or dripping water.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 3R; File No. E27567

cUL Listed per CSA C22.2 No 94; Type 3R File No. E27567

NEMA/EEMAC Type 3R

CSA, File 42184: Type 3R

IEC 60529, IP32

FEATURES

Drip-shield top and seam-free sides, front and back

Galvanized steel lift-off hinges with stainless steel pins

Provisions for padlocking on each draw pull catch

Embossed mounting holes on back of enclosure

Gasketing along top of door

No knockouts

Quick-release door latches

Enclosures are finished with paint over plated surfaces

PRODUCT ATTRIBUTES

Article Number: 38860

Height: 8in

Width: 6in

Depth: 4in

Material: Mild Steel

Finish: Galvanized; Powder Coated

Color: Gray

Color Code: ANSI 61

Body Thickness: 16ga

Door Thickness: 16ga

Mounting: 9.12in

Overall Dimensions: 10.12 x 7.25in

Weight: 5lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately

Panel Mounting Kit and Mounting Bracket Kit must be ordered separately. A Panel Mounting Kit is required to install panel.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE