

Panel Interface Connector, Type 4, Aluminum

CATALOG NUMBER

AC4DB9RJ45GFI



Panel Interface Connector allows programming access to devices inside without opening the enclosure door, reducing the risk of exposing to energized components. The HBE size 32 housing and hinged cover are die cast aluminum. The closed assembly is rated UL Type 4.

INDUSTRY STANDARDS

UL 508A Component Recognized; File No. E61997

FEATURES

The panel interface connector enclosure includes:

A duplex receptacle

A 9-pin D-sub pass-through connector

An RJ 45 pass-through connector

A 3-amp reset

A covered terminal block with screw connections for the internal power connection

PRODUCT ATTRIBUTES

Article Number: 13573

Material: Aluminum

Finish: Powder Coated

Color: Gray

Weight: 1.6lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE