

NEMA 5-15R DIN-Mounted Outlets, With fuse, 3.54x2.44x1.97, Light Gray, Plastic

CATALOG NUMBER

ADINP120F



The DIN rail-mounted NEMA 5-15P electrical receptacle can be quickly fitted and connected inside enclosures, allowing the use of auxiliary products such as hand lamps and power tools. The unit is available with and without fuses.

INDUSTRY STANDARDS

UL Component Recognized; File No. E222026

cUL Component Recognized; File No. E222026

Ingress protection: IP 20

FEATURES

Connection: three cage clamps for solid and stranded wire AWG 20-14 (0.5-2.5mm²)

Housing: plastic, UL94 V-0, light grey

Fuse: Type 5 x 20 mm dia. (Tubular)

Integral mounting clip for 35mm DIN rail, EN 60 715

Mounting position: vertical

Operating / storage temperature -49 F to +158 F (-45 C to 70 C)

Standard NEMA receptacle 5-15R

Protection class I (grounded)

PRODUCT ATTRIBUTES

Article Number: 26094

Material: Composite

Finish: Smooth Matte

Color: Light Gray

Current: 6.3A

Fused: Yes

Weight: 7.1oz

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE