

Hinged-Cover with Knockouts Type 1, 30.00x24.00x6.00, Gray, Steel

CATALOG NUMBER

AHE30X24X6



Hinged-Cover with Knockouts, Type 1, feature a recessed, slotted flush latch for security as well as knockouts on all four sides, making them suitable for a wide variety of applications.

INDUSTRY STANDARDS

UL 50, 50E Listed; Type 1; File No. E27567

cUL Listed per CSA C22.2 No 40; Type 1; File No. E27567

NEMA/EEMAC Type 1

CSA, File 42184: Type 1

IEC 60529, IP30

FEATURES

Butt hinges on door

Various sizes of easily removable concentric knockouts on all four sides

Mounting holes on back of box

Provision for grounding

PRODUCT ATTRIBUTES

Article Number: 51700

Height: 30in

Width: 24in

Depth: 6in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Knockout Pattern Along A Sides: A-B-C-D-E-F-G-H-I

Knockout Pattern Along B Sides: A-B-C-D-E-F-G-H-I

Weight: 45lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE