

Metering Cabinet Type 1, 36x36x12, Gray, Steel

CATALOG NUMBER

AMC363612R



Metering Cabinet, Type 1 houses metering transformers and instrument assemblies in indoor applications. HQ models meet Hydro-Québec requirements. It includes one pre-punched accessory, one potential transformer and one current transformer panel, and a four-lug splitter block.

INDUSTRY STANDARDS

CSA File Number 42184: Type 1

NEMA/EEMAC Type 1

IEC 60529, IP30

FEATURES

Gland plates on top of two-door enclosure for meter connection

Hinged door with pull latch and provision for padlocking

Mounting holes in back

PRODUCT ATTRIBUTES

Article Number: 13788

Height: 36in

Width: 36in

Depth: 12in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Panel: 31.75 x 31.75in

Door Type: Double Door

Weight: 137lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE