

# Swing-Out Panel Kit for Wall-Mount Enclosure, 4.00x2.56x1.42, Zinc Plated, Steel

## CATALOG NUMBER

**ANADFK**



Swing-Out Panel Kits allow mounting standard junction box and NEMA style panels (purchase separately) near the front of the enclosure for easy access to or reading of gauges, switches, pilot lights and other components. Kit consist of heavy-gauge brackets and hinges which are easily installed by drilling small holes in the sides of the enclosure and bolting the brackets in place.

## FEATURES

External screws are stainless steel

internal components are plated steel

All mounting hardware and instructions are provided

Both Kits maintain UL Type 4 rating when properly installed in a Hoffman enclosure

Swing-Out Panel Kits do not fit single-door disconnect enclosures

## PRODUCT ATTRIBUTES

Article Number: 24890

Height: 4in

Width: 2.56in

Depth: 1.42in

Material: Mild Steel

Finish: Zinc Plated

Thickness: 16ga

Max Load: 100lb

Weight: 2.4lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**