

Pressure Compensation, 2.36x2.36x1.46, Lt Gray, Plastic

CATALOG NUMBER

APCDABS



Pressure differentials in a tightly sealed enclosure result from heat generated by electrical and electronic equipment within the enclosure and fluctuations of outside ambient temperature. Pressure compensation devices provide IP66 protection in applications requiring slow pressure equalization. For optimal performance, install two plugs diagonally to each other.

INDUSTRY STANDARDS

UL Type 1, 4, 4X; File No. E234324

CE

IEC/EN 60529, IP66

FEATURES

Air permeability = 42 cubic feet/hour (1,200 liters/hour) at a pressure difference of min. 70 mbar

Easy installation: drill one 1.60-inch (41-mm) diameter hole

Sealing gasket (Nitrile Buna-N Rubber)

Semipermeable membrane inside the plug to filter moisture and dust

Mounting thread M40 with union nut

PRODUCT ATTRIBUTES

Article Number: 16456

Width: 2.36in

Depth: 1.46in

Material: Plastic

Finish: Smooth Matte

Color: Light Gray

Height 1: 2.36in

Height 2: 1.46in

Diameter: 2.36in

Weight: 0.26lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE