

Hinged Window Kit, Type 12, 12.00x12.00x1.49, Gray, Steel

CATALOG NUMBER

APWK1212H

Accp09 Product Photo

Hinged Window Kit, Type 12 is used as a viewing window where access to components mounted behind the window is required. It can be easily mounted by drilling the appropriate mounting holes. Continuous gaskets on all openings maintain UL Type 12 rating.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 12; File No. E61997
CSA Type 12; File No. 42186
NEMA/EEMAC Type 12
IEC 60529, IP55

FEATURES

- Window is .25-in. (6-mm) clear polycarbonate
- Mounting hardware is provided

PRODUCT ATTRIBUTES

- Article Number: 19690
- Material: Polycarbonate; Polycarbonate
- Finish: Powder Coated
- Color: Gray
- Color Code: ANSI 61
- Thickness: 16ga
- Window Size: 10.28 x 10.28in
- Overall Dimensions: 12.00 x 12.00in
- Weight: 6.4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE