

Hinged Window Kit, Type 12, 20.00x16.00x1.49, Gray, Steel

CATALOG NUMBER

APWK2016H



Hinged Window Kit, Type 12 is used as a viewing window where access to components mounted behind the window is required. It can be easily mounted by drilling the appropriate mounting holes. Continuous gaskets on all openings maintain UL Type 12 rating.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 12; File No. E61997

CSA Type 12; File No. 42186

NEMA/EEMAC Type 12

IEC 60529, IP55

FEATURES

Window is .25-in. (6-mm) clear polycarbonate

Mounting hardware is provided

PRODUCT ATTRIBUTES

Article Number: 19710

Material: Polycarbonate; Polycarbonate

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Window Size: 18.28 x 14.28in

Overall Dimensions: 20.00 x 16.00in

Weight: 9.2lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE