

SSLP/SSLP3PT Replacement Door with 3 Point Latch, Type 4X, fits 60x36, SS 304

CATALOG NUMBER

Z60368SS3PT



Replacement door for SSLP and SSLP3PT style enclosures. Maintains NEMA Type 4X rating and converts clamp covers to a 3-point latch. Replacement door is ideal for corrosive enclosure installations that require frequent access and the security of a PowerGlide padlocking handle.

INDUSTRY STANDARDS

Maintains NEMA Type 4X rating when properly installed on HOFFMAN SSLP clamp cover or SSLP3PT stainless steel wall-mount enclosures.

CERTIFICATIONS



FEATURES

Replacement door for SSLP and SSLP3PT enclosures

Seamless foam-in-place gasket

Type 316L stainless steel PowerGlide handle

Internal 3-point latching hardware installed

Data pocket is high-impact thermoplastic

Hinge halves and stainless steel hinge pin

Bonding provision

PRODUCT ATTRIBUTES

Article Number: 14561

Material: Stainless Steel 304

Finish: Brushed #3

Thickness: 14ga

Weight: 55lb

Fits Height: 60in

Fits Width: 36in

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE