

Splitter Box Type 1 4-wire 225 amps, 16.00x16.00x5.00, Gray, Steel

CATALOG NUMBER

ASB224R



Splitter Box, Type 1 splits feeder circuit conductors into multiple branch circuit conductors and comes with pre-installed terminal blocks for three- and four-wire power distribution systems.

INDUSTRY STANDARDS

CSA C22.2 No. 76, File No. 42184: Type 1

NEMA/EEMAC Type 1

IEC 60529, IP30

FEATURES

Various numbers and sizes of combination knockouts are provided on all four sides: see Knockout Size and Spacing Table

Hinged covers

Mounting holes in back

Includes single point ground lug

Ground Splitter (ground bar) accessory available

PRODUCT ATTRIBUTES

Article Number: 13873

Height: 16in

Width: 16in

Depth: 5in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 16ga

Number of Wires: 4

Main Lug Amps CU: 225A

Main Lug Wire Size: 6 AWG - 300 MCM

Main Lug Quantity: 1

Branch Lug Amps CU: 175A

Branch Lug Wire Size: 14 - 2/0 AWG

Branch Lug Quantity: 3

Weight: 17.6lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE