

# Splitter Box Type 1 3-wire 400 amps, 22.00x22.00x6.00, Gray, Steel

## CATALOG NUMBER

**ASB403R**



Splitter Box, Type 1 splits feeder circuit conductors into multiple branch circuit conductors and comes with pre-installed terminal blocks for three- and four-wire power distribution systems.

## INDUSTRY STANDARDS

CSA C22.2 No. 76, File No. 42184: Type 1

NEMA/EEMAC Type 1

IEC 60529, IP30

## FEATURES

Various numbers and sizes of combination knockouts are provided on all four sides: see Knockout Size and Spacing Table

Hinged covers

Mounting holes in back

Includes single point ground lug

Ground Splitter (ground bar) accessory available

## PRODUCT ATTRIBUTES

Article Number: 13868

Height: 22in

Width: 22in

Depth: 6in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Number of Wires: 3

Main Lug Amps CU: 400A

Main Lug Wire Size: 4 AWG - 600 MCM

Main Lug Quantity: 2

Branch Lug Amps CU: 285A

Branch Lug Wire Size: 4 AWG - 600 MCM

Branch Lug Quantity: 2

Weight: 38lb

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**