

Electronic Hygrotherm, 3.03X2.36X1.69, Lt Gray, Plastic

CATALOG NUMBER

ATEMHUM



The Electronic Hygrotherm senses ambient temperature and relative air humidity and adjusts a connected device to maintain temperature and humidity set points.

INDUSTRY STANDARDS

cURus; File No. E164102

CE

FEATURES

Temperature (32-140 F) and humidity (50%-90% RH) adjustment

High switching capacity

Optical function displays (LED) in each control

Mounting clip for 35-mm DIN rail

Change-over contact (relay)

Connection is a 5-pole terminal for AWG 14 max (2.5-mm square); clamping torque .5 Nm (4.4 in-lbs) maximum

Plastic housing UL94V-0

Vertical mounting

Operating voltage is AC 100-240 V with maximum switching capacity of 10 A resistive / 1.6 A inductive at AC 240 V

PRODUCT ATTRIBUTES

Article Number: 16447

Width: 2.36in

Depth: 1.69in

Material: Plastic

Finish: Smooth Matte

Color: Light Gray

Color Code: RAL 7035

Height: 3.03in

Input Voltage AC: 100 – 120V

Weight: 0.2lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE