

Deep-Hinged Window Kit, Type 4 and 4X, 18.19 x 12.14, Gray, Steel

CATALOG NUMBER

AWDH2016N4



Deep-Hinged Window Kits provide protection, visibility and easy access to displays, equipment and components installed behind the viewing area. Window kits are conveniently sized to allow direct mounting in the usable door area of any enclosure with a suitably sized mounting surface.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997 (MS)

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997 (MS)

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997 (SS)

cUL Listed per CSA C22.2, No. 94; Type 3R, 4, 4X, 12; File No. E61997 (SS)

Stainless Steel

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66

Mild Steel

NEMA/EEMAC Type 4, 12

IEC 60529, IP66

FEATURES

Quarter-turn latches for quick access

0.25-in. (6-mm) thick, clear polycarbonate windows for easy viewing

2.5-in. (64-mm) deep to allow for deep controls

Built-in gasket compression stop on back of window kit facilitates flush mounting

Designed for either left or right hinging

Includes mounting template and mounting hardware

Easy-to-remove clip-style hinge pin

Optional Concept handles can be purchased separately to replace the standard quarter-turn latches

PRODUCT ATTRIBUTES

Article Number: 13006
Height: 20in
Width: 16in
Material: Mild Steel
Finish: Powder Coated
Color: Gray
Color Code: ANSI 61
Thickness: 14ga
Window Size: 14.68 x 7.41in
Weight: 12.6lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE