

# Deep-Hinged Window Kit, Type 4 and 4X, 22.19 x12.14, Gray, Steel

## CATALOG NUMBER

**AWDH2416N4**



Deep-Hinged Window Kits provide protection, visibility and easy access to displays, equipment and components installed behind the viewing area. Window kits are conveniently sized to allow direct mounting in the usable door area of any enclosure with a suitably sized mounting surface.

## INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997 (MS)

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997 (MS)

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997 (SS)

cUL Listed per CSA C22.2, No. 94; Type 3R, 4, 4X, 12; File No. E61997 (SS)

Stainless Steel

NEMA/EEMAC Type 3R, 4, 4X, 12

IEC 60529, IP66

Mild Steel

NEMA/EEMAC Type 4, 12

IEC 60529, IP66

## FEATURES

Quarter-turn latches for quick access

0.25-in. (6-mm) thick, clear polycarbonate windows for easy viewing

2.5-in. (64-mm) deep to allow for deep controls

Built-in gasket compression stop on back of window kit facilitates flush mounting

Designed for either left or right hinging

Includes mounting template and mounting hardware

Easy-to-remove clip-style hinge pin

Optional Concept handles can be purchased separately to replace the standard quarter-turn latches

## PRODUCT ATTRIBUTES

---

Article Number: 13007

Height: 24in

Width: 16in

Material: Mild Steel

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 14ga

Window Size: 18.68 x 7.41in

Weight: 14.9lb

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**