

Sequestr Retrofit External Disconnect Type 4X, 34x14x18, Brushed, SS304

CATALOG NUMBER

AXD18SS



Retrofit disconnect enclosures to isolate incoming power and help mitigate arc flash occurrences by moving the disconnect switch to the Sequestr Enclosure. Power is passed-through to the main enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 12

IEC 60529, IP66

CERTIFICATIONS



FEATURES

Interlocks with doors of main control cabinet when the disconnect switch is powered ON

Maintains UL Type 4X rating

Provision for pass-through power into the main cabinet - blank plate for customer modification

Preferred disconnect cutout

Quarter-turn screwdriver slot and 3-point latch

Hidden hinges

Bonding provision on door

Conductive back panel included

Installation hardware and templates included

Continuously welded and ground seams all around

Hinged on right side

PRODUCT ATTRIBUTES

Article Number: 17184
Height: 34.45in
Width: 14in
Depth: 18.12in
Material: Stainless Steel 304
Finish: Brushed #4
Thickness: 14ga
Weight: 77.4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE