

Compact Series Enclosure Type 4X, 175x80x57mm, Gray, Aluminum

CATALOG NUMBER

CCA1886



For use in indoor or outdoor applications, these enclosures protect components and controls in corrosive environments.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 4X, 12, 13; File No. E61997

NEMA/EEMAC Type 4, 4X, 12, 13

CSA File No. 42186: Type 4, 4X, 12, 13

IEC 60529, IP66

FEATURES

Cast Aluminum material

No welded seams or sharp corners

Stainless steel captivated cover screws placed outside sealed area

Two to four grounding screws located on enclosure back wall

Oil-resistant, seamless foam-in-place gasket

Tongue-and-groove sealing construction

Threaded internal bosses provided for mounting optional panels, rails and other components

Mounting holes provided in corners outside of gasketed area

PRODUCT ATTRIBUTES

Article Number: 66620

Height: 6.89in

Width: 3.15in

Depth: 2.24in

Material: Aluminum

Finish: Powder Coated

Color: Traffic Gray

Color Code: RAL 7042

Thickness: 0.16in

Mounting: 2.05 x 6.42in

Weight: 1.1lb

ADDITIONAL PRODUCT DETAILS

A x B x C are internal dimensions.

Purchase panels separately

CCA886, CCA1286 and CCA1886 enclosures have only two mounting holes.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE