

# Compact Series 2 Swivel Tilt 90-Degree Elbow, fits 45x60mm, Lt Gray, Aluminum

## CATALOG NUMBER

**CCS2ESTLG**



Compact Series 2 Swivel Tilt 90-Degree Elbow mounts between a horizontal tube and the enclosure to provide both swivel and tilt options for the machine operator. A 90-degree elbow is incorporated into this design for connecting to a horizontal tube. Swivel allows 300-degree maximum rotation. Tilt allows infinite adjustment from horizontal to 30 degrees. Maximum load is 66 lb. (30 kg).

## FEATURES

Coupling can rotate 300 degrees and tilt from horizontal to 30-degree

Installation hardware, mounting fasteners and gasket included

Assembled Compact Series 2 HMI Arm System has a max weight load of 101 lb. (45.8 kg)

## PRODUCT ATTRIBUTES

Article Number: 41899

Height: 1.77in

Width: 2.36in

Material: Aluminum

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Weight: 6.8lb

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**