

Compact Series 2 Flange Elbow Coupling 15-Deg, fits 45x60mm, Lt Gray, Aluminum

CATALOG NUMBER

CCS2FEC15LG



Compact Series 2 Flange Elbow Coupling, 15-Degree attaches directly to the enclosure for applications where a vertical tube is not required, enabling 300-degree enclosure rotation and 15-degree angle tilt. Maintenance-free bearing is steel and polyamide. Includes access plate for easy wire installation.

FEATURES

Coupling can rotate 300 degrees with stop

Enclosure is mounted at a 15-degree incline angle

Installation hardware, mounting fasteners and gasket included

Assembled Compact Series 2 HMI Arm System has a max weight load of 101 lb. (45.8 kg)

PRODUCT ATTRIBUTES

Article Number: 15678

Height: 1.77in

Width: 2.36in

Material: Aluminum

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Weight: 2.4lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE