

CS480 Straight Tube, 1250mm, Brushed, SS304

CATALOG NUMBER

CCSS48T125



CS480 Straight Tube provides structural integrity and acts as conduit for equipment wiring.

INDUSTRY STANDARDS

IEC 60529, IP66

FEATURES

Wall thickness 3.6-mm

Outer diameter of 48.3-mm

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

PRODUCT ATTRIBUTES

Article Number: 42619

Height: 49.21in

Width: 1.9in

Depth: 1.9in

Material: Stainless Steel 304

Finish: Polished

Thickness: 0.14in

Weight: 10lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE