

We connect and protect

# Drive Access Door for Concept HMI Enclosure, 13.15x4.61x0.56, Lt Gray, Steel

## Catalog Number

CDACCDR  
CONCEPTOIDriveCovertrans Product Photo

- Drive door can be installed only on enclosures to access internal disk drives. Key-locking latch is included. Maintains NEMA Type 12 rating.

## Features

- Installation template and hardware are included
- Cannot be used on 120-mm deep enclosures
- Hinges have RAL 9005 black polyester powder paint finish

## PRODUCT ATTRIBUTES

- Article Number: 15286
- Height: 13.15in
- Width: 4.61in
- Depth: 0.56in
- Material: Mild Steel
- Finish: Powder Coated
- Color: Light Gray
- Color Code: RAL 7035
- Thickness: 16ga
- Weight: 1.9lb

## Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/HOFFMAN](https://nVent.com/HOFFMAN) |