

Concept Console Type 4X, 38.00x24.00x15.00, Brushed, SS304

CATALOG NUMBER

CFC382416SS



Concept Console provides a convenient surface for mounting and monitoring components. Ergonomically designed so users can sit or stand while working on a sloped surface. Console features a large internal capacity for mounting components and controls.

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA Type 3R, 4, 4X, 12, 13

Meets NEMA Type 3RX requirements

FEATURES

Solid bottom

Corner-formed doors

External-formed 90-degree body flange

20-degree sloped-top cover for 38.00-in. (965-mm) tall console or 30-degree top cover for 48.00-in. (1219-mm) console

Quarter-turn stainless steel latches hold top cover securely closed

Door props hold top cover open at 90-degrees

Integral water-shedding trough

Collar studs for optional back panel

Optional side panels (mounted to collar studs) expand equipment mounting space

Tool-to-open 3-point latch on front access door; door is removable and reversible; 170-degree full-access opening

Seamless foam-in-place gasket

Bonding provision on door; grounding stud on body

Provision for data pocket on lower front door

Easy-to-remove clip-style hinge pins

PRODUCT ATTRIBUTES

Article Number: 87330
Height: 38in
Width: 24in
Depth: 15in
Material: Stainless Steel 304
Finish: Brushed #4
Thickness: 14ga
Data Pocket: Small
Weight: 137lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE