

# Concept Panel, fits 16.00x12.00 inch Enclosure, Galvanized, Mild Steel

## CATALOG NUMBER

**CP1612G**



Concept panels are taller and wider than corresponding NEMA-size panels.

## FEATURES

Painted white or conductive finish

Include a formed flange along any side that is longer than 22.20 in (564 mm)

Optional wood panels are made of 3/4-in plywood, pre-cut and pre-drilled to install on panel mounting studs in the rear of the cabinet

## PRODUCT ATTRIBUTES

Article Number: 26439

Height: 14.2in

Width: 10.2in

Material: Mild Steel

Finish: Galvanized

Thickness: 12in

Type: Conductive

Gauge: 12ga

Weight: 4.5lb

## ADDITIONAL PRODUCT DETAILS

---

Catalog number CP4230 is used on Concept disconnect enclosures.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**