

Concept HMI Enclosure Black Handle Type 4, 450x550x180mm, Light Gray, Mild Steel

CATALOG NUMBER

CP455518



A traditional landscape-oriented HMI enclosure with handles made of light-gray steel, the Concept HMI Enclosure is unique among HMI enclosure systems when you need a range of customization options. This pendant- or pedestal-mounted system has many possible configurations and modifications, including a removable front plate that makes it easy to install HMI components, an optional door panel can be mounted in the hinged rear door and the ability to accommodate cutouts anywhere on the enclosure.

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File Number E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997

NEMA Type 4, 12

IEC 60529, IP66

FEATURES

Pre-drilled hole in top for pendant arm mounting

Pedestal mounting when enclosure is inverted

Integral aluminum handle extrusions have a comfort grip that extends the length of the profile; available in black or blue

Hinged rear corner-formed door has a single-point latch, seamless foam-in-place gasket and panel studs

Aluminum removable front plate is .125-in aluminum

Grounding stud on body; bonding provision on door

Simple easy-to-remove and install hinge pins with built-in captive clip

High-torque threadless studs and fasteners on door for mounting optional door panel

PRODUCT ATTRIBUTES

Article Number: 14734

Height (H): 17.72in

Width (W): 21.65in

