

We connect and protect

Concept Wallmount 1/4-Turn Latch Type 4X, 16x16x10, Brushed, Stainless 304

Catalog Number

CSD161610SS

Csd16126Ss Concept Type 4X

- For indoor or outdoor applications that require corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush quarter-turn latches for secure closure.

Industry Standards

- UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997
- cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997
- Mounting brackets required to meet UL/CSA external mounting requirements.
- NEMA/EEMAC Type 3R, 4, 4X, 12, 13
- IP66
- IEC 60529, IP66
- Meets NEMA Type 3RX requirements

Features

- Minimum-width body flange provides maximum body opening
- External formed 90-degree body flange
- Panel mounting studs fit optional Concept panels and other accessories
- Mounting holes in back of body for direct mounting or for optional external mounting brackets
- Type 316 stainless steel hidden hinges promote clean aesthetic appearance
- Corner formed doors are interchangeable and easily removed by pulling clip-style hinge pins
- Provision on door (except when B = 12 inch (305mm)) for thermoplastic data pocket
- Provision on door (except when B = 12 inch (305mm)) for optional doorstop kit
- Quarter-turn latches furnished with flush slotted insert
- Seamless foam-in-place gasket
- Self-grounding latch system with double seal
- Bonding provision on door; grounding stud on body

- Furnished hardware kit consists of panel-mounting nuts, panel-grounding hardware and sealing washers for wall-mounting hole

PRODUCT ATTRIBUTES

- Article Number: 12856
- Height: 16in
- Width: 16in
- Depth: 10in
- Material: Stainless Steel 304
- Finish: Brushed #4
- Body Thickness: 16ga
- Door Thickness: 16ga
- Mounting: 14.50 x 14.50in
- Latch Quantity: 1
- Weight: 24lb
- Latch Type: Quarter-Turn

Additional Product Details

Purchase panels separately. Optional stainless steel, composite and aluminum panels are also available for most sizes.

Optional NEMA style steel and stainless steel panels require conversion kit catalog number CCPM4.

Warning

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

nVent-logo

Our powerful portfolio of brands:

- Caddy
- Erico
- Hoffman
- IlSCO
- Schroff
- Trachte

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

