

Concept Sloped Top Wallmount 1/4-Turn Latch Type 4X, 30x24x12, Brushed, SS 304

CATALOG NUMBER

CSD302412SSST



For indoor or outdoor applications that require a sloped top and corrosion protection from chemicals and water. Concept Enclosures feature streamlined styling with an attractive stroked finish and flush, stainless steel quarter-turn latches for secure closure.

INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No 94; Type 3R, 4, 4X, 12; File No. E61997

Mounting brackets required to meet UL/CSA external mounting requirements.

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IP66

IEC 60529, IP66

Meets NEMA Type 3RX requirements

FEATURES

20 degree sloped top prevents pooling of liquids and accumulation of other debris

Minimum-width body flange provides maximum body opening

External formed 90-degree body flange

Panel mounting studs fit optional Concept panels and other accessories

Mounting holes in back of body for direct mounting or for optional external mounting brackets

Type 304 stainless steel hidden hinges promote clean aesthetic appearance (two hinges on models under 36 in. in height; three hinges for models 36 in. and taller)

Corner-formed doors are interchangeable and easily removed by pulling clip-style hinge pins

Provision on door for thermoplastic data pocket

Provision on door for optional door stop kit

Seams continuously welded and ground smooth

Stainless steel quarter-turn latches furnished with flush slotted insert

Seamless foam-in-place gasket

Self-grounding latch system with double seal

Bonding provision on door; grounding stud on body

Furnished hardware kit consists of panel-mounting nuts, panel-grounding hardware and sealing washers for wall-mounting holes

Installation instructions

PRODUCT ATTRIBUTES

Article Number: 26015

Height: 30in

Width: 24in

Depth: 12in

Material: Stainless Steel 304

Finish: Brushed #4

Body Thickness: 16ga

Door Thickness: 14ga

Mounting: 28.50 x 22.50in

Latch Quantity: 2

Weight: 62lb

ADDITIONAL PRODUCT DETAILS

Purchase panels separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE