

# Concept Sloped-Top Enclosure Type 4, 36.00x30.00x12.00, Light Gray, Mild Steel

## CATALOG NUMBER

**CSD363012ST**



Concept Sloped Top Enclosures support Lean factory principles and are ideal when the miniaturization of controls calls for smaller control cabinets or for applications requiring the mounting of controls at an ergonomic height when attached to equipment.

## INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997

Mounting brackets required to meet UL/CSA external mounting requirement.

NEMA/EEMAC Type 4, 12, 13

IP66

IEC 60529, IP66

## FEATURES

Bonding provision on door and body

Panel-mounting studs fit optional Concept panels and other accessories

Corner-formed door

Simple easy-to-remove and install hinge pins with built-in captivation clip

High-torque threadless studs and fasteners on door

Illustrated instruction sheet

External formed body flange channels away liquids

Door opens 210 degrees

Seamless foam-in-place gasket

Quarter-turn latches

Mounting holes in back of body for optional external mounting brackets

Larger sizes support 19-in. rack mounting

Door alignment device on doors wider than 30-in.

Minimum-width body flange provides maximum door opening

20-degree sloped top

**PRODUCT ATTRIBUTES**

---

|                           |
|---------------------------|
| Article Number: 14473     |
| Height: 36in              |
| Width: 30in               |
| Depth: 12in               |
| Finish: Powder Coated     |
| Material: Mild Steel      |
| Color: Light Gray         |
| Color Code: RAL 7035      |
| Body Thickness: 14ga      |
| Door Thickness: 14ga      |
| Panel Size: 34.2in        |
| Panel Size: 28.2in        |
| Mounting: 38.86 x 28.50in |
| Latch Quantity: 2         |
| Latch Type: Quarter-Turn  |
| Weight: 95lb              |

**ADDITIONAL PRODUCT DETAILS**

---

Purchase panels separately.

**WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**