

Swing-Out Rack Frame, fits 24.00x24.00 inch enclosure, Gray, Mild Steel

CATALOG NUMBER

CSF2424



Swing-Out Rack Frames provide 120-degree swing-out access for 19-in. rack equipment.

FEATURES

Welded rack frame mounts to front flange

Distance from frame to door surface is 1.32 in. (33 mm) for solid doors and 1.07 in. (27 mm) for window doors

Mounting hinge and latching hardware provided

PRODUCT ATTRIBUTES

Article Number: 78730

Height: 24in

Width: 24in

Material: Mild Steel

Finish: Powder Coated

Color: White

Thickness: 14ga

Weight: 5.6lb

ADDITIONAL PRODUCT DETAILS

Order separately clip nut package catalog number XNM5 and screws XSM5 (metric) or AN1032 and screws AS1032 (English).

Swing-Out Rack Frame cannot be mounted on adjustable mounting kit.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE