

Concept Fixed Window Kit, Type 4, fits 310x360mm, Gray, Aluminum

CATALOG NUMBER

CWF3136



Concept fixed window kit can be used as a viewing window on larger standard nVent HOFFMAN enclosure doors. Pre-assembled kit is secured to front opening of enclosure by mounting screws.

INDUSTRY STANDARDS

UL 508A, 508, File Number E61997: Type 4 and Type 12 (Fixed Window)

UL 508A, 508, File Number E61997: Type 12 (Hinged Window)

(Fixed Window)

NEMA Type 4 and 12

IEC 60529, IP66

(Hinged Window)

NEMA Type 12

IEC 60529, IP66

FEATURES

Aesthetic die-cast aluminum frame

0.188-in. (5-mm) thick, clear polycarbonate window

Furnished window frame caps conceal mounting screws

PRODUCT ATTRIBUTES

Article Number: 41570

Product Family: Concept

Material: Aluminum

Finish: Powder Coated

Color: Gray

Color Code: ANSI 61

Thickness: 0.15in

Window Size: 9.96 x 10.86in

Weight: 5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE