

Handle Concept Padlock Type 3, 4, 4X, 12, 3.54x1.00x1.57, Black, Mild Steel

CATALOG NUMBER

CWHPTO



Handles replace the standard slotted insert on all Concept wall-mount enclosures.

FEATURES

A zinc die-cast key lock handle (CWHK) is available for applications requiring quick access and security

A padlocking handle (CWHPTO), also zinc die-cast, accommodates a padlock with up to a 5/16-in. locking bar

Each latch system can be converted from clockwise to counter-clockwise opening

Kit includes handle, sealing washer, wave washer, instruction manual and keys if handle is lockable

PRODUCT ATTRIBUTES

Article Number: 79410

Height: 3.54in

Width: 1in

Depth: 1.57in

Product Family: Concept

Material: Mild Steel

Finish: Powder Coated

Color: Black

Weight: 0.48lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE