

# Seismic Free-Stand DA Cabinet Type 3R 4 4X 12, 90x36x46, Brushed, SS304

## CATALOG NUMBER

**D903646SDAS**



Ideal where front or front and rear access is required. These enclosures have sturdy unibody construction and include 19-inch rack angles to support equipment. These enclosures are ideal for housing and protecting networking and communications equipment from corrosion, liquid, and seismic events. 36-inch wide models include integral, vertical cable management that supports copper and fiber networking cables.

## INDUSTRY STANDARDS

UL 508A Listed; Type 3R, 4, 4X, 12; File No. E61997

cUL Listed per CSA C22.2 No. 94; Type 3R, 4, 4X, 12; File No. E61997

NEMA/EEMAC Type 3R, 4, 4X, 12

E.I.A. RS310-D

CSA, File No. 42186, Type

IEC 60529, IP66

OSPHD Approved OPM -0248-13

NEBS-Telecordia GR-63-CORE Zone 4: Tested with 1000 lb. of equipment installed

Meets California Building Code (CBC) requirements

## FEATURES

Reinforced stainless steel construction protects networking/communication equipment from corrosion, liquid, and seismic activity

Six seismic bottom-mounting plates made of painted plated steel for 5/8-inch diameter anchors

Lifting eyes installed for ease of handling

Rack angles included are infinitely adjustable from front-to-rear supporting multiple networking/communication equipment configurations

36-inch wide models include integral, vertical, RU-aligned fingers for supporting copper and fiber networking cables

AC models available for heat management

Data pockets included for equipment information management/organization

PRODUCT ATTRIBUTES

|                               |
|-------------------------------|
| Article Number: 30537         |
| Height: 90.26in               |
| Width: 36.14in                |
| Depth: 46.16in                |
| Material: Stainless Steel 304 |
| Finish: Brushed #3            |
| Thickness: 12ga               |
| Rack Units: 42U               |
| Weight: 840lb                 |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE