

Mounting Bracket Kit for IS/GSC Boxes, fits B=6.00 or 8.00, Plated, Steel

CATALOG NUMBER

DMFK1



Mounting bracket kits are field-installable. DMFK1 and DMFK2 include two 14-gauge steel external mounting brackets and fasteners. CMFK, CMFKSS, and CMTGFT include four brackets per kit.

FEATURES

Plastic mounting foot kits are rated for 500 lb (227 kg) maximum load

Sealing washers are provided with each kit to maintain Type 4 and 12 after installation

Stainless steel and plastic mounting bracket kits are rated to Type 4X

All hardware is included

PRODUCT ATTRIBUTES

Article Number: 60580

Height (H): 1.5in

Width (W): 4.75in

Depth (D): 0.07in

Material: Mild Steel

Finish: Plated


Thickness (T): 14ga

Fastener Thread Size: #10-32

L: 4.75in

Weight: 0.32lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE